


Discover more details and matching accessories online!

Particularly user-friendly moisture analyser with high-quality halogen quartz glass heater- also available as version with [d] = 10 mg, ideal for recurring rapid tests

Features

- KERN DAB 200-2: Version with lower resolution, whereby the switch-off criterion is reached faster, which saves time. Ideal for quick tests and spot checks
- Backlit graphic display, digit height 14 mm
 - 1 Active drying process
 - 2 Active heating profile
 - 3 Active switch-off criteria
 - 4 Previous drying time
 - 5 Current temperature
 - 6 Current moisture content in %

- 400 W halogen-quartz glass heater
- Suitable for temperature-insensitive samples
- Helpful observation window above the sample
- Internal memory for automatic sequence of 15 complete drying processes and 5 drying processes carried out
- The last value measured remains on the display until it is replaced by a new measurement
- 50 sample plates included
- On the internet, you will find a practical application handbook containing many examples, field reports, settings and tips for each KERN moisture analyser

- Note: both models are also available in infrared version, see *internet*

STANDARD



1 DAY

OPTION



KERN	DAB 100-3	DAB 200-2
Readability [d] Weight/Moisture (%)	0,001 g / 0,01 %	0,01 g / 0,05 %
Weighing capacity [Max]	110 g	200 g
Reproducibility weight of sample 2 g*	0,15 %	1,5 %
Reproducibility weight of sample 10 g*	0,03 %	0,3 %
Display after drying (Display can be switched over at any time)		
Moisture [%] = Moisture content (M) from wet weight (W)	20 % - 100 %	
Dry content [%] = Dry weight (D) from (W)	100 % - 20 %	
Moisture content (M)	Absolute value in [g]	
Temperature range (in steps up to)	40 °C - 199 °C (1 °C)	
Drying modes	Standard drying, Gentle drying, Rapid drying	
Switch-off criteria	Automatic switch-off (2 mg loss in weight in 45 s)	
	Time controlled switch-off (3 min - 99 min 59 s, 10 s increments)	
	Manual switch-off at the press of a button	
Recall of measurement/ Log output	Interval can be set from 1 s - 10 min (Only when used with printer or PC)	
Overall dimensions W×D×H	240×365×180 mm	
Net weight	4,82 kg	
Option Calibr. Certificate DAkks accr. Mass	963-127	
Option Factory calibration certificate Temperature	964-305	

* application-dependent