

**PRODUCT**

## ESD Safe Spray Bottle

16 and 32oz ESD spray bottles for use in cleanroom environments.

Part of a wide range of ESD static dissipative spray bottles and dispensers available in a selection of sizes from stock.

Please note this is sold as the bottle only, and contains no contents.



**ANALYSIS**

### SOLVENT EXTRACTION STUDIES

The identity and amount of materials extracted from the bottles into commonly used solvents in a seven day period at room temperature have been determined.

### CAN BE USED WITH

- Water (H<sub>2</sub>O)
- 1,1,1-Trichloroethane (TCE)
- Isopropyl Alcohol (IPA)
- Methylene Ketone (MEK)

### SOLVENT STABILITY

The structure provided for the anti-stat (N, N-diethanol octanamide) is that of a very stable molecule. By its chemical nature, it will have no chemical reactivity with the solvents. The pH of the water solutions was the same (ca. 5.9) before and after the seven day period. No colour change or other physical change was noted for any of the solvents used in this study.

PRODUCT CODE	DESCRIPTION	SIZE (oz)	NOTES
146-0020	ESD Safe Spray Bottle	16	Each
146-0021	ESD Safe Spray Bottle	32	Each

To request a quotation or for more information, please call **+44 (0)1473 836200**  
email [info@antistat.co.uk](mailto:info@antistat.co.uk) or visit [www.antistat.co.uk](http://www.antistat.co.uk)