

EN ZM12.SIDE Installation Manual

DE ZM12.SIDE Installationsanleitung FR

ZM12.SIDE Manuel d'installation

ES ZM12.SIDE Manual de instalación

Doc. ID: PU-200.100.81-xxZ (2019-01-10-MR1)

Side Mount Bracket Seitlicher Montagewinkel Kit de montage latéral Soporte de montaje lateral

Product Description

The ZM12.SIDE is a mechanical accessory to mount the device sideways with or without utilizing a DIN-rail to save installation depth.

The two aluminum brackets and the black plastic slider of the unit have to be detached, so that the ZM12.SIDE steel bracket can be mounted.

For sideway DIN-rail mounting, the removed aluminum brackets and the black plastic slider need to be mounted on the ZM12.SIDE steel bracket.

The order number ZM12.SIDE contains one bracket and four screws, which are


needed for sideways DIN-rail mounting.

Intended Use

This mechanical accessory is designed for DIN-rail devices. Check the product datasheet of the DIN-rail device to confirm that it is suitable for the desired device.




Size (width x height x depth) 65x145x44mm 160g / 0.33lb Weight



Headquarters: PULS GmbH, Elektrastr. 6, 81925 Munich, Germany, www.pulspower.com							
Germany	+49 89 9278 0	France	+33 478 668 941	Austria	+43 2764 3213	Switzerland	+41 56 450 18 10
China	+86 512 62881820	North America	+1 630 587 9780	Singapore	+65 6684 2310	United Kingdom	+44 1525 841001
The information in this document is believed to be accurate and reliable and may change without notice							

PULS



Installation Instructions

- 1) Detach the two aluminium brackets by removing the four screws with a Torx screwdriver (Torx 10). Save the screws for step 3.
- 2) Remove the plastic lock mechanism by using a flat-blade screwdriver to move the lock downwards while at the same time push the plastic slide upwards. Detach the plastic slide.
- Mount the steel brackets with the same screws from the DIN-Rail brackets using caution not to over-tighten the screws! Recommended tightening torque is 0.6Nm. (5.3lb.in).

Preparation for DIN-Rail mounting

Install the two aluminium brackets and the plastic slide (detached from the unit before) onto the side mounting plant with the additional screws provided.

